




ADOGO014MSS0010B11

Connection technology



Product characteristics

Socket

M16 connector

Electrical data

Electrical design		DC
Operating voltage [V]		30 DC
Current rating [A]		3

Environment

Ambient temperature [°C]		-25...90
Protection		IP 67

Mechanical data

Design		straight
Material body		PUR
Material nut		Brass; nickel-plated
Weight [kg]		0.793


Electrical connection

Connection		PUR cable / 10 m; 2 x 0.34 mm <sup>2</sup> (14 x Ø 0.15 mm) + 9 x 0.25 mm <sup>2</sup> (7 x Ø 0.2 mm); Ø 7.5 mm
Sheath colour		black

Wiring

Core colours

BK	black
BN	brown
BU	blue
GN	green
GY	grey
PK	pink
RD	red
VT	lilac
WH	white
YE	yellow



⌋ A	BN
⌋ C	GY/PK
⌋ E	BK
⌋ G	PK
⌋ J	GN
⌋ L	BU
⌋ N	RD/BU
⌋ O	VT
⌋ P	WH
⌋ S	GY
⌋ T	YE

U: not used  
M: not used

Remarks

Pack quantity	[piece]	1
---------------	---------	---