



Part no.: 50040097
KD 01-5-BA
Connector



Figure can vary

Contents

- Technical data
- Electrical connection

Part no.: 50040097 – KD 01-5-BA – Connector

Technical data

Electrical data

Performance data

Operating voltage	Max. 60 V AC/DC
Rated operating current	4,000 mA

Connection

Connection 1

Type of connection	Connector with screw terminals
Function	Voltage supply
Thread size	M12
Type	Female
Handle body material	Metal
No. of pins	5 -pin
Encoding	A-coded
Design	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

Cable properties

Wire cross section	0.75 mm ²
AWG	18

Mechanical data

Width across flats	18 mm
Max. cable hole	6 ... 8 mm

Environmental data

Ambient temperature, operation	-40 ... 85 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	85369010
eCl@ss 8.0	27069190
eCl@ss 9.0	27069190
ETIM 5.0	EC001578
ETIM 6.0	EC001578

Electrical connection

Connection 1	
Type of connection	Connector with screw terminals
Function	Voltage supply
Thread size	M12
Type	Female
Handle body material	Metal

Part no.: 50040097 – KD 01-5-BA – Connector

Connection 1	
No. of pins	5 -pin
Encoding	A-coded
Design	Axial
Lock	Screw fitting, nickel-plated diecast zinc, recommended torque 0.6 Nm, self-locking

