

## Data sheet

### CM 201 (201-1AA20)

#### Technical data

<b>Order no.</b>	<b>201-1AA20</b>
Type	CM 201
<b>General information</b>	
Note	-
Features	Dual terminals 2x11 clamps, red/blue Passive
<b>Clamp parameter</b>	
Terminal voltage max.	DC 60 V
Terminal current max.	10 A
<b>Isolated group</b>	
Number of clamps	11-11
Color of clamps	red-blue
Binding of potential	unbound-unbound
Potential group current, max.	10 A-10 A
<b>Housing</b>	
Material	PPE / PA 6.6
Mounting	Profile rail 35 mm
<b>Mechanical data</b>	
Dimensions (WxHxD)	25.4 mm x 76 mm x 80 mm
Weight	90 g
<b>Environmental conditions</b>	
Operating temperature	0 °C to 60 °C
Storage temperature	-25 °C to 70 °C
<b>Certifications</b>	
UL508 certification	yes