

Pneum. contact metal OD6mm F+valve ang.



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 7466
Specification	Pneum. contact metal OD6mm F+valve ang.
HARTING eCatalogue	https://b2b.harting.com/09140007466

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	With shut-off Angled

Version

Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Limiting temperature	-20 ... +85 °C Tube outer diameter
Operating pressure	≤10 bar
Tube outer diameter	6 mm

Material properties

Material (contacts)	Brass
Material (seal)	HNBR (hydrated NBR)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
California Proposition 65 substances	Nickel
California Proposition 65 substances	Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	10
Net weight	17.04 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140189263
eCl@ss	27440204 Contact for industrial connectors