

## M12 Power Male PE Contact Crimp 2,5mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 100 9930
Specification	M12 Power Male PE Contact Crimp 2,5mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/21011009930">https://b2b.harting.com/21011009930</a>

### Identification

Category	Contacts
Series	Circular connectors M12
Identification	Power
Type of contact	Crimp contact
Description of the contact	FE contact 24.8 mm length

### Version

Gender	Male
Manufacturing process	Turned contacts
Details	use with M12 Power female contacts

### Technical characteristics

Conductor cross-section	2.5 mm <sup>2</sup>
Conductor cross-section	AWG 14
Performance level	1

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

PROFINET	Yes
----------	-----

## Commercial data

Packaging size	50
Net weight	0.53 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140229303
eCl@ss	27440204 Contact for industrial connectors