

Product information

49 21 A01

Precision Circlip Pliers

For external circlips on shafts

DIN 5254 B



MM  $\angle 90^\circ$



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Large contact faces on the tips: no distortion of circlips, easy fitting
- Bolted joint: precise, zero backlash operation of pliers
- Internal opening spring, protected and captive
- Non-slip plastic coating on the handles
- Angled tips
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

General

Article No.	49 21 A01
EAN	4003773048817
Pliers	grey atramentized
Handles	with non-slip plastic coating
Weight	100 g
Dimensions	130 x 63 x 11 mm
Standard	DIN 5254 B
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Size of shaft	Ø 3 – 10 mm
Tips (diameter)	0.9 mm

technical change and errors excepted





Spring inside the joint: the spring is protected inside the precisely bolted joint. It does not hinder work and cannot get dirty or lost.