

H0,5/14 ZH OR SV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



- in multipack bag (5 x 100 pcs.)
- Weidmüller colour code
- DIN colour code

General ordering data

Material number	9004440000
Short text for material	H0,5/14 ZH OR SV
Article - short description	Wire end ferrule, 0.5 mm ² , 8 mm, Colour code: Weidmüller, orange
EAN	4008190198473
Qty.	500 pc(s).

H0,5/14 ZH OR SV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Approvals

Approvals CCSAUS; GOSTME25

Product data

Conductor cross-section	0.5 mm ²	Contact surface length (L2)	8 mm
Collar height (A)	5 mm	Collar width (B)	3 mm
Contact surface diameter (D1)	1.4 mm	Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.3 mm		

Classifications

ETIM 2.0	EC000005	ETIM 3.0	EC000005
ETIM 4.0	EC000005	UNSPSC	31-16-31-02
eClass 4.1	27-06-07-01	eClass 5.1	27-40-02-01
eClass 6.0	27-40-02-01		

Dimensions

Length	15 mm	Width	3.5 mm
--------	-------	-------	--------

Product notes

Description sub-group

- Polypropylene conical cable entry
- Heat-resistant up to 105°C
- Cable entry from a not readily flammable material on request

For conductors from 2 No. 0.5 to 2 No. 16 mm² (2 No. AWG 20 to 2 No. AWG 6)

Tin-plated copper
 Dimensional tolerances to DIN 46228 part 4

Description of article Twin wire end ferrule, orange