

**Short**

Short body external thread banana plugs. Brass body, beryllium copper spring, nickel plated.


Supplied with lug and nut.

**460:** 4-40x3/8

**461:** 4-40x1/2

**462:** 6-32x3/8

**463:** 6-32x1/2



**Standard**

Standard body, external threaded stud, banana plugs. Brass body, beryllium copper spring, nickel plated.

Supplied with lug and nut.

Rated at 15 Amps AC.

**401:** 6-32x3/8


**103:** 6-32x1/2

**404:** 6-32x3/4

**405:** 8-32x3/8

**406:** 8-32x1/2

**407:** 8-32x3/4



**Standard**

Standard body, external threaded stud, banana plugs. Brass body, beryllium copper spring, nickel plated.

Supplied with lug and nut.

Rated at 15 Amps AC.

**102:** 6-32x3/8


**432:** 6-32x1/2

**433:** 6-32x3/4

**434:** 8-32x3/8

**435:** 8-32x1/2

**436:** 8-32x3/4



**145**  
Standard banana plug.  
Brass body, beryllium  
copper spring, nickel  
plated.  
Supplied with threaded  
stud and nut.  
Rated at 15 Amps AC.

**100**  
Standard body internal  
thread banana plug. Brass  
body, berrilium copper  
spring, nickel plated.  
Supplied with lug and 6-  
32 screw.  
Rated at 15 Amps AC.