

Datasheet

Art.No. 96.051.4153.1

Female connector with strain relief RST20I5S B1 ZR2 SW

Connector RST20i5, 5 pole, female, screw connection, 250/400V, 20A, for cable diameters 10-14 mm, color of coding: black, color of housing: black



Approvals



Technical data

General

Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Strain relief	Yes
Pollution degree	3
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	3, N, PE, 2, 1

Connection Data

Connection cross section solid	4 mm ²
Connection cross section stranded max.	4 mm ²
Terminations per pole	1

Model

Model	female
Number of poles	5
Connection type	Screw connection
Degree of protection (IP)	IP66/68 (3m;2h) /IP69K

Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C

Surface finish	Silver-plated
----------------	---------------

Dimensions

Length	80.4 mm
Width	34.6 mm
Height	34.6 mm

Classification

ECLASS 8.1	27440605: Plug-in connector for plug-in building installation
ETIM 5.0	EC002560: Plug-in connector for plug-in building installation
ETIM 4.0	EC002560: Plug-in connector for plug-in building installation