

### BU-4062-N-XX-@ (UL® Listed Test Probe PVC Wire)



- 4mm, Right angle, shrouded, banana plug
- Uses 18 AWG (65/36) UL 1855, with a flexible PVC jacket.
- Length is designated in inches by the “XX” in the part number.  
Standard lengths are: 12”, 18”, 24”, 39”, 48”, 60” and 72”
- Material: Probe – Stainless Steel, #8-32 threads for attachments  
Banana Plug – Nickel plated Beryllium Copper and Brass  
Cover -- Polypropylene
- Ratings:
  - Operating Voltage: 1,000V CAT III
  - Current: 20 Amps
  - Operating Temperature: -40°C to 80°C
- Color: The “@” in the model number represents color. Available colors:  
-0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White
- RoHS 3 Compliant, CE Certified