

Offset clamp, with adjustable support screw, complete



Application:

For clamping workpieces.

Version:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted



| | |
|---|------------------|
| Art. no. | 26222 030 |
| For table grooves according to DIN 650 | 14 mm |
| Suitable screw DIN 787 | M12 x 100 mm |
| Min./max. clamping range | 28-56 mm |
| Groove width | 14 mm |
| Span iron length | 125 mm |
| Span iron width | 40 mm |
| Thread dimension | M12 |
| Thread length | 49 mm |
| Thickness | 20 mm |
| Distance | 44 mm |
| Length | 40 mm |

EAN-Code

402077207 1295