

Swarf containers, manual tipping

with floor-level emptying option, mobile

Application:

An indispensable aid for collecting and separating liquids from solids and for transporting waste, bulk materials, chips and mass produced parts of all types.

Execution:


- Skip with sliding handle
- Stable sheet steel structure with edge reinforcement, base frame made of section steel
- With perforated sheet insert for chip collection, hole diameter 3 mm, division 6 mm and drain valve 1"
- Fork pockets with protection against accidental slipping and tipping
- Easily movable with two wheels and one steering wheel (from content of 600 litres with two steering wheels) made of solid rubber, diameter 250 x 60 mm, one steering wheel with wheel brake

Advantage:

- With floor-level emptying option
- Portable thanks to the integrated wheels, meaning they can be used anywhere
- Manual tilting of the trough ensures that it can be emptied without leaving any material behind, with locking protection that prevents it tipping over

Delivery:

Goods supplied without packaging as standard. Packaging on request.



Art. no.	50266 646
Volume	1 m ³
Length	1420 mm
Width	1340 mm
Tipper edge height	870 mm
Height	1290 mm
Fork pocket clearance	465 mm
Fork pocket size (W x H)	170 x 55 mm
Number of wheels	4 PCS
With drain valve	Yes
With stacker seat tilt function	No
With perforated sheet	Yes
Load-carrying capacity	300 kg
Surface	Lacquered
Colour	Black grey RAL 7021
Gross Weight	173.000 kg
Product Group	5AI

EAN

4052462060777