

Special cable ties

Ty-Grip™ Hook & Loop fasteners

Characteristics

These handy ties are very easy to release and re-use, making them ideal for applications where changes are anticipated or continuous access is required.

- Quick bundling and re-adjustable tension
- No risk of over-tightening the cables, which makes the Ty-Grip™ Hook & Loop fasteners ideal for specific applications in fibre optics, computer network wiring, telecom cables, etc.
- Multiple colours available for identifying specific bundles
- Different sizes available to accommodate varying bundle diameters
- Screw-mount and self-adhesive mounting bases provide multiple mounting options

Technical Information FO Series

Material hook side	Polyamide
Material loop side	Low density Polyethylene
Temperature range	-20°C to +104°C
Colour	Standard colour: black
Flammability rating	UL 94 HB*
Peel-off strength	0.8N/cm

Technical Information FOL Series

Material hook side	Polyamide
Temperature range	-20°C to +93°C
Colour	Standard colour: black - see note after table
Flammability rating	UL 94 HB
Peel-off strength	0.8N/cm



FO series loop ties are ideal for wrapping pre-determined bundle diameters thanks to the convenient slotted head.



FOL series buckle ties provide added strength and stability thanks to the high performance polyamide buckle.

Product Ref.	Maximum bundle diameter [mm]	Length L [mm]	Width W [mm]	Tensile strength [N]	Quantity [pieces]
FO SERIES LOOP TIES					
F0200-40-0	50.8	228.6	12.7	180	10
F0200-50-0	50.8	228.6	19.1	220	10
F0350-40-0	88.9	330.2	12.7	180	10
F0350-50-0	88.9	330.2	19.1	220	10
F0350-50-0-FR*	88.9	330.2	19.1	220	10
FOL SERIES BUCKLE TIES					
FOL300-50-0	76.2	304.8	19.1	220	10
FOL500-50-0	127.0	457.2	19.1	220	10

Replace "-0" in the Product Reference by the corresponding colour code: 1 = brown, 2 = red, 3 = orange, 4 = yellow, 5 = green, 6 = blue, 8 = grey and 9 = white



* Suffix FR is Flame Retardant version

Special cable ties

Ty-Grip™ Hook & Loop fasteners

Characteristics

These handy ties are very easy to release and re-use, making them ideal for applications where changes are anticipated or continuous access is required.

- Quick bundling and re-adjustable tension
- No risk of over-tightening the cables, which makes the Ty-Grip™ Hook & Loop fasteners ideal for specific applications in fibre optics, computer network wiring, telecom cables, etc.
- Multiple colours available for identifying specific bundles
- Different sizes available to accommodate varying bundle diameters
- Screw-mount and self-adhesive mounting bases provide multiple mounting options

Technical Information FOS and FOR Series

Material hook side	Polyamide
Material loop side	Low density Polyethylene
Temperature range	-20°C to +104°C
Colour	Standard colour: black*
Flammability rating	UL 94 HB
Peel-off strength	0.8N/cm



FOS series strip ties are pre-cut which makes bundling easy.



FOR series rolled hook and loop allows customers to conveniently cut pieces to desired lengths, eliminating waste.

Product Ref.	Maximum bundle diameter [mm]	Length L [mm]	Width W [mm]	Tensile strenght [N]	Quantity [pieces]
FOS SERIES STRIP TIES					
FOS150-50-0	38.1	152.4	19.1	220	10
FOS320-50-0	81.3	304.8	19.1	220	10
FOS500-50-0	127.0	457.2	19.1	220	10
FOR SERIES ROLLED STRIP					
FOR180-50-0	Various	4572.0	19.1	220	1
FOR180-50-0-FR**	Various	4572.0	19.1	220	1

* Standard colour: black

Replace "-0" in the Product Reference by the corresponding colour code: 1 = brown, 2 = red, 3 = orange, 4 = yellow, 5 = green, 6 = blue, 8 = grey and 9 = white

For example: FOS150-50-2 defines a red FOS150-50 type fastener



** FOR180-50-0-FR is made of flame retardant material

Contact your Sales Office for Product Availability in the other colours