

CAN-PLUG-MALE (SUB-D) 90°

Screw terminals up to 1Mbits/s

Bus Connection Plug 90°

SUB-D9 (female), screw terminals


max. 1 Mbit/s with switchable terminal resistors

CANopen

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Technical Data

Terminating resistor	integrated, switchable
Transfer rate	max. 1 Mbit/s with switchable terminal resistors
Connection cross section	max. 1 mm ²

General data

Protection	IP20
Dimensions H × W × D	65×48×16 mm
Temperature range	0...+60 °C (storage temperature -25...+80 °C)

Commercial data

country of origin	DE
customs tariff number	85369010

minimum order quantity

1