

electronic pocket vernier calipers

angled internal/external measuring surfaces, knife-edge callipers

Mitutoyo

Application:

For carrying out internal measurements, measuring wall thickness in holes, carrying out measurements within a groove

Execution:

- Digimatic
- IP67
- AUTO OFF
- ABSOLUTE system for reliable measurement
- High-contrast display

Advantage:

- Suitable for special or difficult to reach measuring points

Delivery:

Delivered in box



Art. no.	32018 099
Brand	MITUTOYO
Manufacturer Part Number	573-751-20
Min./max. length measuring range in inches	0-6 in
Depth gauge rod	Without
IP protection class	IP 67
With drive wheel	Yes
Length of jaw	40 mm
Design	Metric, Imperial
Digit height	9 mm
Digit increment	0.01 mm
Digit increment in inches	0.0005 in
Type of locating	With locking screw
With mm / inch switching	Yes
Battery designation	1,5 V SR44
Number of rechargeable batteries/batteries	1 PCS
Weight of rechargeable battery/battery	0.002 kg
Battery voltage	1.55 V
Type of rechargeable battery/battery	Silver oxide
Calibration Group	A
ISO	13385-1
Functions	Absolute function, With mm / inch switching, ABS function
Gross Weight	0.520 kg
Product Group	3MA

EAN

4946368727011