

## Parallel vice

With fixed jaws, front opening action

**ORION**<sup>®</sup>

### Execution:

- Made of steel, forged
- Hardened, ribbed and fixed steel jaws
- Adjustable guide

### Advantage:

- Mounting holes for pipe clamping jaws
- Spindle protected from dirt and damage by covering
- Hardened anvil surface



|                                 |                  |
|---------------------------------|------------------|
| <b>Art. no.</b>                 | <b>51063 026</b> |
| <b>Brand</b>                    | ORION            |
| <b>Manufacturer Part Number</b> | 51063026         |
| <b>Jaws width</b>               | 125 mm           |
| <b>Min./max. clamping width</b> | 0-150 mm         |
| <b>Clamp in depth</b>           | 80 mm            |
| <b>Weight</b>                   | 11 kg            |
| <b>Colour</b>                   | Blue             |
| <b>Gross Weight</b>             | 10.300 kg        |
| <b>Product Group</b>            | 586              |

### EAN

4053625051045