


REIKU-Kabelschutz-Wellrohre

REIKU Tubings for Cable Protection



PA	Polyamid	<i>polyamide</i>
TP	thermopl. Polyesterester	<i>thermopl. polyesterester</i>
R	Wellrohr	<i>corrugated tubing</i>
R	Roboterversion	<i>robot</i>
F	Fahrzeugversion	<i>vehicle version</i>
I	Isolier-Version	<i>insulation version</i>
B	schwarz	<i>black</i>
G	grau	<i>grey</i>
	Nennweite	<i>Nominal width</i>
F	Feinprofil	<i>fine profile</i>
G	Grobprofil	<i>broad profile</i>

PA RR G-10 F

PA R R G / PA R R B Polyamid 12, für Roboter/*polyamide 12, for robots*

Bestell-Nr./Article no <i>grau/grey</i>	<i>schwarz/black</i>	NW mm	für/for M/PG	d2	d1	Radius mm (stat.) (dyn.)	kg/100 m	(VE) m (PU) m
PA R R G-07G	PA R R B-07G	07	10/07	10,0	6,4	15 40	2,20	100
PA R R G-10F	PA R R B-10F	10	12/09	13,0	9,4	20 50	2,60	50
PA R R G-12F	PA R R B-12F	12	16/11	15,8	11,8	25 65	3,50	50
PA R R G-17F	PA R R B-17F	17	25/16	21,2	16,5	30 80	5,50	50
PA R R G-23F	PA R R B-23F	23	32/21	28,5	22,6	35 90	9,20	50
PA R R G-23G	PA R R B-23G	23	32/21	28,5	21,7	40 100	9,20	50
PA R R G-29F	PA R R B-29F	29	40/29	34,5	27,5	45 120	12,00	50
PA R R G-29G	PA R R B-29G	29	40/29	34,5	27,5	50 120	12,00	50
PA R R G-36G	PA R R B-36G	36	50/36	42,5	35,9	60 180	16,00	30
PA R R G-48G	PA R R B-48G	48	63/48	54,5	46,5	70 200	22,00	30
PA R R G-52G	PA R R B-52G	52		63,0	52,0	125 300	36,50	10/30
PA R R G-70G	PA R R B-70G	70		82,5	70,0	150 350	51,00	10/30
PA R R G-95G	PA R R B-95G	90		106,0	87,5	170 400	75,00	10/30

PA R F B Polyamid 12, verstärkt, schwarz/*polyamide 12, strengthened, black*

UL 105 °C

grau auf Anfrage/grey on request

UL recognized File E 168970 (M) 105°C ab Nennweite 17/*from NW 17 onwards*

Bestell-Nr./Article no	NW mm	für/for M/PG	d2	d1	Radius mm (stat.) (dyn.)	kg/100 m	(VE) m (PU) m
PA R F B-10 F	10	10/09	13,0	9,4	25 60	3,10	50
PA R F B-12 F	12	12/11	15,8	11,6	30 80	4,50	50
PA R F B-17 G	17	25/16	21,2	14,8	50 100	8,10	50
PA R F B-23 G	23	32/21	28,2	21,2	60 110	11,70	50
PA R F B-29 G	29	40/29	34,5	27,5	75 160	17,10	50
PA R F B-36 G	36	50/36	42,0	34,4	110 250	18,90	30
PA R F B-48 G	48	63/48	54,0	46,1	170 300	26,60	30
PA R F B-52 G	52		62,0	52,0		41,00	10/30
PA R F B-70 G	70					60,00	10/30

PA R A B Polyamid 12, schwarz/*polyamide 12, black*

Bestell-Nr./Article no	NW mm	für/for M/PG	d2	d1	Radius mm (stat.) (dyn.)	kg/100 m	(VE) m (PU) m
PA R A B-10F	10	10/09	13,0	9,4	20 50	2,60	50
PA R A B-12F	12	12/11	15,5	11,8	25 65	3,50	50
PA R A B-17F	17	25/16	21,0	16,5	30 80	5,50	50
PA R A B-23G	23	32/21	28,0	22,3	40 100	9,20	50
PA R A B-29G	29	40/29	34,0	28,2	50 120	12,00	50
PA R A B-36G	36	50/36	42,0	35,9	60 180	16,00	30
PA R A B-48G	48	63/48	54,0	46,5	70 200	22,00	30
PA R A B-52G	52		62,8	52,0	125 300	36,50	10/30
PA R A B-70G	70		82,0	70,0	150 (350)	51,00	10/30