













Plug-in units – for CompactPCI, VME64x

Individual components

inserter/extractor handles, type IEL/IET, fixing material

Order Information



| Fixing material | Item | 3 U | 3 U | | 6 U | | Qty/PU | Part no. |
|---|------|---|--------|--------|--------|--------|-----------------------------------|-----------|
| | | | < 8 HP | ≥ 8 HP | < 8 HP | ≥ 8 HP | | |
| Printed board bracket Zn die-cast | 1 |  | 1 | 1 | - | - | 1 piece (SPG 10) ¹⁾ | 60807-181 |
| Pozidrive panhead screw M2.5 × 6, St, nickel-plated, not for 0.1" offset | 3 |  | 2 | 2 | 2 | 2 | 100 | 21101-219 |
| Slotted panhead screw with Torx 8 M2.5 × 6, St, zinc-plated, self-securing thread not for 0.1" offset | 3a |  | 2 | 2 | 2 | 2 | 100 | 24560-159 |
| Washer 2.7, DIN 125, St, nickel-plated | 4 |  | 2 | 2 | 2 | 2 | 100 | 21100-721 |
| Raised Pozidrive countersunk panhead screw M2.5 × 8, St, nickel-plated | 5 |  | 1 | 1 | - | - | 100 | 21100-429 |
| Raised countersunk panhead screw with Torx 8 M2.5 × 8, St, nickel-plated | 5a |  | 1 | 1 | - | - | 100 | 24560-164 |
| Pozidrive/slotted collar screw M2.5 × 12.3, St, nickel-plated | 6 |  | 1 | 3 | - | 2 | 100 | 21101-101 |
| Plastic sleeve, for form hole 5.9 x 3.3 PA, UL 90 V-2, grey | 7 |  | 1 | 3 | - | 2 | 100 | 21100-464 |
| Metal sleeve, for form hole 5.9 x 3.3, press-in Stainless steel | 7a |  | 1 | 3 | - | 2 | 100 | 21100-662 |
| Pozidrive panhead screw for IEL/IET handle with 0.1" offset M2.5 × 10, nickel-plated steel | 8 |  | 2 | 2 | 2 | 2 | 100 | 21101-220 |
| Torx panhead screw M2.5 × 7, St, nickel-plated, Torx 8, | 9 |  | 1 | 1 | 2 | 2 | 100 | 24560-147 |

1) SPQ (standard pack quantity): Part number includes 1 piece, but delivery is exclusively made in standard pack quantity (SPQ); please order at least the SPQ quantity or a multiple