

32 Zoll Indoor Display High Brightness

Panel Specifications	
Panel model	32inch TFT LED
Max Resolution	1920*1080
Aspect Ratio	16:09
Pixel Pitch	0.36375*0.36375
Viewing Angle	89/89/89/89
Contrast Ratio	4000:1
Brightness	2500cd/m
Response Time	6.5ms
General Information	
Processor	RK3588 Quad-core ARM Cortex-A76 + Quad-core ARM Cortex-A55 (4 Core+4 Core)
GPU	OpenGL ES 1.1、2.0、3.2, OpenCL 2.2 and Vulkan
NPU	6TOPs
Operation system	Android 12
DDR4/RAM	8GB
Flash	128GB
RJ45	RJ45*2, 100M/1000Mbps
WiFi	Optional 2.4GHz、2.4GHz+BT、2.4GHz+5GHz+BT(Optional)
USB	Android USB3.0 *2; EXT USB*6
MIPI CSI	Support 8-megapixel MIPI CSI Camera , with built-in 8M ISP
Storage Temp	-20 to 70 degree
Working Temp	-5 to 45 degree
Storage Humidity	5-95%
Working Humidity	10-90%
Connectivity	
LAN	RJ45 Port
WIFI	Built-in WIFI 802.11B/G/N
4G(Optional)	WCDMA
Ports	
USB 3.0	x2
HDMI Output	x2
HDMI Input	x1
TF Card	x1
RJ45	x2
4G SIM (Optional)	x1
Supported Media formats	
Video	H.264, MKV, WMV9, MPEG 1/2/4, HD Divx, Xvid, RM/RMVB;
Image	BMP/PNG/GIF/JPEG
Audio	MP3,WMA,WAV,EAAC+, MP2 dec, Vorbis (Ogg), AC3, FLAC, APE, BSAC;
Scrolling text	txt
Functions	
Rolling subtitles	H.264, MKV, WMV9, MPEG 1/2/4, HD Divx, Xvid, RM/RMVB;

Power Memory	BMP/PNG/GIF/JPEG
Split Screen	MP3,WMA,WAV,EAAC+, MP2 dec, Vorbis (Ogg), AC3, FLAC, APE, BSAC;
Software Update	txt
Display Mode	Support Portrait & Landscape display mode
Play mode	Repeat all, single repeat, order play
General Info.	
Material	Metal+Aluminum+4mm laminated glass
Color	Black
Mount	Ceiling Mount
Certification	CE/ROHS/FCC
Supporting 24/7 operation	