



- Soldering bath
- 100 W, 230 V
- Inside Ø 17,4 mm, depth 22 mm
- Different temperatures available
- Magnastat temperature control
- Horizontal stand
- For lead free solder

W101 H Soldering bath

Product no.: T0056109399N

| | |
|--|---------------------|
| Dimensions L x W x H (mm) | 350 x 90 x 50 |
| Dimensions L x W x H (inches) | 13.78 x 3.54 x 1.97 |
| Weight (approx.) in kg | --- |
| Voltage | 230 V |
| Power | 100 W |
| Channels | --- |
| Temperature range (depends on tool) °C | --- |
| Temperature range (depends on tool) °F | --- |
| Temperature accuracy °C | --- |
| Temperature accuracy °F | --- |
| Temperature accuracy for hot air °C | --- |
| Temperature accuracy for hot air °F | --- |
| Temperature stability °C | --- |
| Temperature stability °F | --- |
| Equipotential bonding socket | --- |
| Display | --- |
| Additional vacuum pump | --- |
| Max. hot air flow rate l/min (depends on tool) | --- |
| Capacity l/min | --- |
| Max. vacuum | --- |
| Interface | --- |