

Product information

86 01 180

Pliers Wrench

Pliers and a wrench in a single tool



- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings - working directly on chrome!
- Increased gripping capacity thanks to two additional setting positions: variable gripping of all widths across flats up to 40 mm
- 10 % less weight with the same stability
- Practical adjustment scale: a laser-cut scale allows the wrench opening to be set before gripping
- Also excellent for gripping, holding, pressing and bending workpieces
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Fast adjustment by pushing a button directly on the workpiece
- No unintentional shift of the gripping jaws and no slipping of the joint
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Chrome vanadium electric steel, forged, oil-hardened




General

Article No.	86 01 180
EAN	4003773084273
Pliers	grey atramentized
Head	polished
Handles	plastic coated
Weight	230 g
Dimensions	180 x 46 x 15 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Jaw thickness (joint) (B2)	8.0 mm
Joint thickness (B3)	12.0 mm
Tips thickness (B1)	5.0 mm
Adjustment positions	15
Capacities for nuts	Ø 1 1/2 Inch
Capacities for nuts	40 mm



technical change and errors excepted

