

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1122191018](#)  
**Status:** **Active**  
**Overview:** [Woodhead ArcArrest Connector System](#)  
**Description:** Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7, Three Grommets Included

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E145922

**General**

Product Family Wiring Devices  
 Series [112219](#)  
 IP Rating IP69K  
 NEMA Configuration N/A  
 Overview [Woodhead ArcArrest Connector System](#)  
 Product Literature Order No 987651-4741  
 Product Name ArcArrest  
 Receptacle Type N/A  
 Specialty Switch-Rated  
 Type Plug  
 UPC 78172558538  
 Woodhead Yes

**Physical**

Cord Grip Body Size F4 1"  
 Flange Yes  
 Flip Lid No  
 Gender Male  
 Length 178.99mm (7.047")  
 Locking Blade N/A  
 Poles 2

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 30.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 125V / 250V AC

**Material Info**

Engineering Number ARC30MHDAB04

**Reference - Drawing Numbers**

Sales Drawing 1122191024-000



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[112219 Series](#)