



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch body
Device short name	ZCMD
Design	Miniature
Body type	Fixed
Associated head	ZCE65 ZCE27 ZCE62 ZCE64 ZCE28 ZCEG1 ZCE11 ZCE67 ZCE01 ZCE10 ZCEF2 ZCE09 ZCE21 ZCE24 ZCE08 ZCE07 ZCE66 ZCE63 ZCE29 ZCEF0 ZCE13 ZCE02 ZCE14 ZCE06
Body material	Zamak
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contact operation	Slow-break Slow-break, break before make

Complementary

Product compatibility	XCMD
Electrical connection	Removable cable
Cable length	6.56 ft (2 m)
Cable composition	5 x 0.75 mm ²
Wire insulation material	PvR
Contacts insulation form	Zb
Contacts material	Silver plated contacts
Positive opening	With
Minimum actuation speed	6 m/min
[Ui] rated insulation voltage	300 V 3)UL 508 400 V 3)IEC 60947-5-1 300 V 3)CSA C22.2 No 14
Maximum resistance across terminals	25 mOhm conforming to IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	4 KV IEC 60664 4 kV IEC 60947-1
Short-circuit protection	6 A cartridge fuse gG

Electrical durability	5000000 Cycles, DC-13 120 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 24 V, 4 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 cycles, DC-13 48 V, 3 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C
Maximum Width	1.18 in (30 mm)
Height	1.97 in (50 mm)
Depth	0.63 in (16 mm)
Net Weight	0.14 lb(US) (0.065 kg)

Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
-------------------------------------	----------------------------

Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901686071
Nbr. of units in pkg.	1
Package weight(Lbs)	0.51 lb(US) (0.23 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Package 1 Height	0.300 dm
Package 1 width	1.500 dm
Package 1 Length	1.500 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------