

## Plug-In Timer - Plug-in timer, Digital clock timer, 7-Day or 24-Hr programming, 230 VAC, 50/60 Hz, 16 A, 20 Setpoint Programs, SPDT, F style plug with enhanced child protection - PT 600 F 192

Item 161500011 / EAN-Code 1220000330733



### PRODUCT DESCRIPTION

The PT 600 F digital plug-in time switch features 20 memory spaces and allows precise switching, even after a power failure or a clock change. Thanks to a range of programs, such as the daily program, weekly program or random switching, and with a very short switching time of only 1 minute, you can realize a wide variety of highly-flexible switching options. In addition, a manual switch enables quick manual switching on and off without affecting programming.

### FEATURES

- ▶ 24-hour or 7-day applications
- ▶ 20 setpoint programs
- ▶ Three preset adjustable block programs
- ▶ Menu driven programming
- ▶ Manual override with status indicator
- ▶ Battery backup
- ▶ 1 minute switching time

### APPLICATIONS

- ▶ Indoor Lighting Control

### TECHNICAL DATA

General	
Model Number	161500011
Description	Plug-in timer, Digital clock timer, 7-Day or 24-Hr programming, 230 VAC, 50/60 Hz, 16 A, 20 Setpoint Programs, SPDT, F style plug with enhanced child protection - PT 600 F 192
UPC Code	999999999993
Country of Origin (Intermatic)	CHINA
Warranty Period	1-Year
Usage Environments	Indoor
Harmonized Code	9107.00.8000
Packaging Unit	56
EAN Code	1220000330733
Housing type	Surface mounted

Control Specifications	
Minimum ON/OFF Times	1 min
Operation Mode	24 hour; 7 day
Backup Type	Battery
Backup Protection Time	3 Years
Mechanism Type	Digital/Electrical
Minimum ON/OFF Operations	1

Mechanical Specifications	
Number of Plugs	1
Plug Configurations	Plug Type F

Dimensions	
------------	--

Product Dimensions (H x W x D) mm	146 x 73 x 75 mm
Product Dimensions (H x W x D) in	5.75 x 2.87 x 2.95 in

#### Material Specifications

Color	Gray
Cover Color	Light Gray
Housing Material	ABS plastic

#### Load Ratings

Resistive Load Ratings Ranges	16 A / 250 VAC, 21A / 250 VAC (UL)
Inductive Load Ratings Ranges	8 A. 250 VAC

#### Electrical Specifications

Input Voltage Range(s)	230 VAC $\pm$ 10%, 50/60 Hz
Input Voltage Frequencies	50 or 60 Hz

#### Packaging

Shipping Weight (kg)	0.295
Shipping Weight (lbs)	0.65
Product Weight (kg)	0.23
Product Weight (lbs)	0.506
Unit Carton Dimensions (H x W x D) in	6.4 x 3.5 x 3.245 in
Units Per Pallet	999

#### Environmental Specifications

Temperature (operation)	-10 - 55 °C / 14 - 131 °F
-------------------------	---------------------------

#### Standards and Certifications

Other Certifications and Compatibilities	CE; REACH
Standards and Guidelines	EN 60730-1, Mode of operation and additional properties: Type 1.B
RoHS Certification	Yes