

## START Flex Low Output

START Flex IP65 840 2750lm  
0068128



### Product features

- 5 metre IP65 LED reel with pre-attached 3M adhesive type; equipped with 300 LEDs; 2750lm per 5m (550lm per 1m); 24V; 4000K; CRI80; SDCM 3; Compatible with emergency packs: 0046600, 0046601



## PRODUCT OVERVIEW

Product name	START Flex IP65 840 2750lm
Technology	LED
Housing	Other
Mount	Other
General application	Hospitality, Retail
ETIM Class	EC002706
E-number FI	4276598
Warranty	5 years
Fixture luminous flux (lm)	2750
Luminaire efficacy (lm/W)	115
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	120
Beam Angle (°)	N/A
Photobiological Risk Group	RG1
Total power consumption (W)	24
Electrical protection	Class III
Dimmable	Yes
Dimming method	Other
Housing colour	Beige
IP rating	IP65
IK rating	IK00
Product EAN number	5410288681283

## DATA TABLE

### General data

Product name	START Flex IP65 840 2750lm
Technology	LED
Housing	Other
Mount	Other
General application	Hospitality, Retail

## START Flex Low Output

START Flex IP65 840 2750lm  
0068128

Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002706
E-number FI	4276598
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	2750
Luminaire efficacy (lm/W)	115
Colour temperature (K)	4000
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	120
Beam Angle (°)	N/A
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	24
Mains voltage (V)	24V
Electrical protection	Class III
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Other
Drive current (mA)	1000
Glow Wire Test (°C)	650
Lamp Energy Label (class)	F

### Lifetime data

Lifespan L70 B50	54000
Lifespan L70 B10	54000
Lifespan L80 B10	50000
Lifespan L90 B10	44000

### Physical data

Housing colour	Beige
IP rating	IP65
IK rating	IK00
Nominal Product Length (mm)	5000
Nominal Product Width (mm)	10
Nominal Product Height (mm)	4
Weight (kg)	0.3

### Packaging

Single packaging type	Carton
Product EAN number	5410288681283
Packaging single length / height (cm)	23.5
Packaging single width (cm)	22.5

## START Flex Low Output



START Flex IP65 840 2750lm  
0068128

Packaging single depth (cm)	3.0
DUN14 (outer)	15410288681280
Units per outer package	20
Packaging outer length / height (cm)	49.0
Packaging outer width (cm)	34.0
Packaging outer depth (cm)	24.0

### Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

## PHOTOMETRY




Distance [m]	Cone diameter [m]	E <sub>0</sub> [lx]	E <sub>10</sub> [lx]	E <sub>30</sub> [lx]
0.5	1.59	724	84	75
	1.36	87.9*	14	19
1.0	3.19	161	14	19
	2.72	87.9*	14	19
1.5	4.78	80	8	9
	4.08	87.9*	14	19
2.0	6.38	46	4	5
	5.45	87.9*	14	19
2.5	7.97	29	2	3
	6.81	87.9*	14	19
3.0	9.56	20	1	2
	8.17	87.9*	14	19

Distance [m]      Cone diameter [m]      Illuminance [lx]

— C0 - C180 (Half beam angle: 107.4°)  
— C90 - C270 (Half beam angle: 115.8°)

## TECHNICAL DRAWINGS




# SYLVANIA

START Flex Low Output  
START Flex IP65 840 2750lm  
0068128



0068128



**24**  
kWh/1000h




2019/2015

START Flex Low Output  
START Flex IP65 840 2750lm  
0068128



0068128



**24**  
kWh/1000h



2019/2015