

Precision scales EHA

KERN

Application:

Thanks to its compact and robust design, bright display and high precision, this series is ideal for use in laboratories, quality control settings, production and in schools and teaching, e.g. biology, chemistry and physics lessons

Execution:

- Thanks to its compact and robust design, bright display and high precision, this series is ideal for use in laboratories, quality control settings, production and in schools and teaching, e.g. biology, chemistry and physics lessons
- Large, impact-resistant weighing tray made of stainless steel, easy and hygienic to clean
- Especially flat design
- Ergonomically optimised control panel with buttons and high-contrast LCD display
- Secure and non-slip placement with rubber feet
- Level and foot screws for precise levelling of the scales come as standard, producing the most accurate weighing results
- CAL calibration program for setting accuracy
- compact all-round model

Delivery:

with mains adapter



Art. no.	49000 001
Brand	KERN
Manufacturer Part Number	EHA 1000-1
Type description	EHA 1000-1
Max. weight measuring range	1000 g
Digit increment, weight	0.1 g
Plate size	120 x 120 mm
Material of cover panel	Stainless steel
With unit counting	Yes
Min. item weight	1 g
Reproducibility	0.3 g
Linearity	0.3 g
Housing dimensions (LxWxH)	225 x 160 x 50 mm
Gross Weight	0.750 kg
Product Group	447

EAN

4045761229518