

All-steel screw clamps 120–600 mm clamping width

With slip and spindle lock, 2-C handle

ATORN[®]

Application

For sprung and elastic clamping of a range of workpieces.

Version

- Fixed clamp made of cold-drawn profile steel, hardened and galvanised
- Sliding clamp drop-forged, hardened and galvanised
- Movable pressure plate with integrated spindle safety device
- Smooth running, burnished steel spindle with trapezoidal thread

Advantage

- Ergonomic two-component handle for optimum force transmission

Art. no.	51105 060
Max. clamping width	600 mm
Overhang	120 mm
Rail cross-section L x W	12 x 25 mm
Material of the grip handle	2-component plastic



EAN-Code

4050293648126