

Flat magnetic grips, hard ferrite core, steel jacket

With bore hole and countersink

ORION[®]

Application:

Auxiliary materials with universal application during clamping, assembling, lifting and welding operations, and for installing in devices etc.

Version:

- With hard ferrite core
- Surface galvanised
- Magnetic shielding
- With bore hole and countersink
- Operating temperature up to 100°C

Advantage:

- Fastening option from inside with a screw



Art. no.	51146 730
Outer diameter	20 mm
Height	6 mm
Bore diameter	4.2 mm
Adherence strength	40 N

EAN-Code

4039247261918