



- Unit purifies air at up to 4 workplaces
- Constant Flow Control (CFC) guarantees automatic air flow regulation for each working place independent of the connected workplaces
- Electronic filter control with optical and acoustical filter alarm
- Efficiency test via USB port
- 4 wheels to allow easy movement of the unit
- Remote control via RS 232 port
- Low noise level
- 4 kits available
- The fume extraction unit Zero Smog 4V Kit 1 Funnel is easy to install and operate. It is designed for use as a small central system. The kit is supplied complete with 1 pcs flexible hose, flexarm, funnel nozzle, valve and bracket, ready for installation at the workplace. A powerful, maintenance-free turbine provides continuous fume extraction at a maximum air extraction rate of 230 m³/h. With setting constant flow control the adjustable turbine speed avoiding unnecessary waste of suction power and saving energy.

Zero Smog 4V Kit 1 Funnel

Code No.: T0053662699

Dimensions W x D x H (mm)	345 x 325 x 505
Dimensions W x D x H (Inch)	13,58x12,79x19,88
Weight (ca) in kg	19
Voltage	220 - 240 V, 50/60 Hz
Heating output	275 VA
Noise level (distance 1 m) dB(A)	< 48
Max. vacuum	---
Capacity m ³ /h	230
Pre filter	Pre filter mat class F7
Cartridge Volume Extraction	Particle filter H13, Wide band gas filter (50 % Active carbon + 50 % Chemisorb)
Max. capacity	1-4 workplaces
Interface RS232 (Remote control)	All system functions can be operated and remotely monitored via the RS232 port.
USB interface	on
WX compatible	on

Weller Tools GmbH
Carl-Benz-Straße 2
74354 Besigheim
Germany

Phone: +49 (0) 7143 / 580-0
Fax.: +49 (0) 7143 / 580-108
Email: info@weller-tools.com
Web: www.weller-tools.com