




FUSES & FUSEHOLDERS

5x20mm Glass and Ceramic Fuses


5x20mm Quick Blow Glass Fuses

TYPE NO.	RATING
CF0520F/125	125mA
CF0520F/160	160mA
CF0520F/200	200mA
CF0520F/250	250mA
CF0520F/315	315mA
CF0520F/400	400mA
CF0520F/500	500mA
CF0520F/630	630mA
CF0520F/800	800mA
CF0520F/1	1A

TYPE NO.	RATING
CF0520F/1.25	1.25A
CF0520F/1.6	1.6A
CF0520F/2	2A
CF0520F/2.5	2.5A
CF0520F/3.15	3.15A
CF0520F/4	4A
CF0520F/5	5A
CF0520F/6.3	6.3A
CF0520F/8	8A
CF0520F/10	10A
CF0520F/12.5	12.5A
CF0520F/15	15A
CF0520F/16	16A
CF0520F/20	20A

- Quick blow (F) IEC60127-2/2
- Glass cartridge, nickel plated end caps
- Break capacity 35A/250V or 10 x In whichever is greater at above 3.5A
- Colour coded available
-   BSI,  approved (200mA to 6.3A)




CF0520F




5x20mm Time Delay Glass Fuses

TYPE NO.	RATING
CF0520T/100	100mA
CF0520T/125	125mA
CF0520T/160	160mA
CF0520T/200	200mA
CF0520T/250	250mA
CF0520T/315	315mA
CF0520T/400	400mA
CF0520T/500	500mA
CF0520T/630	630mA
CF0520T/800	800mA

TYPE NO.	RATING
CF0520T/1	1A
CF0520T/1.25	1.25A
CF0520T/1.6	1.6A
CF0520T/2	2A
CF0520T/2.5	2.5A
CF0520T/3.15	3.15A
CF0520T/4	4A
CF0520T/5	5A
CF0520T/6.3	6.3A
CF0520T/8	8A
CF0520T/10	10A
CF0520T/12.5	12.5A

- Time delay (F) IEC60127-2/3
- Glass cartridge, nickel plated end caps
- Break capacity 35A/250V or 10 x In whichever is greater at above 3.5A
- Colour coded available
- Spiral element or plated solder section for superior characteristics
-   BSI,  and BSI approved (200mA to 6.3A)



CF0520T




5x20mm Quick Blow Ceramic Fuses

TYPE NO.	RATING
CF0521CF/100	100mA
CF0521CF/125	125mA
CF0521CF/160	160mA
CF0521CF/200	200mA
CF0521CF/250	250mA
CF0521CF/315	315mA
CF0521CF/400	400mA
CF0521CF/500	500mA
CF0521CF/630	630mA
CF0521CF/800	800mA
CF0521CF/1	1A

TYPE NO.	RATING
CF0521CF/1.25	1.25A
CF0521CF/1.6	1.6A
CF0521CF/2	2A
CF0521CF/2.5	2.5A
CF0521CF/3.15	3.15A
CF0521CF/4	4A
CF0521CF/5	5A
CF0521CF/6.3	6.3A
CF0521CF/7.5	7.5A
CF0521CF/8	8A
CF0521CF/10	10A
CF0521CF/12.5	12.5A

- Quick blow (F) IEC60127-2/1
- Ceramic cartridge, nickel plated brass end caps
- High break capacity 1500A/250V
- Sand filled
-   and BSI approved (250mA-10A)



CF0521CF




5x20mm Time Delay Ceramic Fuses

TYPE NO.	RATING
CF0521CT/100	100mA
CF0521CT/125	125mA
CF0521CT/160	160mA
CF0521CT/200	200mA
CF0521CT/250	250mA
CF0521CT/315	315mA
CF0521CT/400	400mA
CF0521CT/500	500mA
CF0521CT/630	630mA
CF0521CT/800	800mA
CF0521CT/1	1A

TYPE NO.	RATING
CF0521CT/1.25	1.25A
CF0521CT/1.6	1.6A
CF0521CT/2	2A
CF0521CT/2.5	2.5A
CF0521CT/3.15	3.15A
CF0521CT/4	4A
CF0521CT/5	5A
CF0521CT/6.3	6.3A
CF0521CT/7.5	7.5A
CF0521CT/8	8A
CF0521CT/10	10A
CF0521CT/12.5	12.5A

- Time delay (T) IEC60127-2/5
- Ceramic cartridge, nickel plated brass end caps
- High break capacity 1500A/250V
-  200mA- 15A  BSI 1A-6.3A
- Sand filled

CF0521CT



FUSES & FUSEHOLDERS

6.3x25mm (1/4"x1") Glass & British Plug Top Fuses

6.3x25mm Quick Blow Glass Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CF06325FG/250	250mA	CF06325FG/3	3A
CF06325FG/500	500mA	CF06325FG/5	5A
CF06325FG/800	800mA	CF06325FG/7	7A
CF06325FG/1	1A	CF06325FG/10	10A
CF06325FG/2	2A	CF06325FG/13	13A

- Quick blow (F)
- Glass cartridge, nickel plated end caps
- Break capacity, 35A/250V (250mA to 1A), 100A/250V (1A to 3A), 200A/250V (3A to 13A)
- To IEC 127



6.3x25mm Time Delay Glass Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CF06325TG/250	250mA	CF06325TG/3	3A
CF06325TG/500	500mA	CF06325TG/5	5A
CF06325TG/800	800mA	CF06325TG/7	7A
CF06325TG/1	1A	CF06325TG/10	10A
CF06325TG/2	2A	CF06325TG/13	13A



- Time delay (T)
- Glass cartridge, nickel plated end caps
- Break capacity, 35A/250V (250mA to 1A), 100A/250V (1A to 3A), 200A/250V (3A to 13A)
- To IEC 127



6.3x25mm British Plug Top Fuses

TYPE NO.	RATING
CFA1362/1A	1A
CFA1362/2A	2A
CFA1362/3A	3A
CFA1362/5A	5A
CFA1362/7A	7A
CFA1362/10A	10A
CFA1362/13A	13A

- Power dissipation max 1 Watt
- Ceramic tube, silver - plated copper end caps
- Break capacity, 6000A, 264VAC, 50Hz, p.f. 0.3 - 0.4
- BS1362, IEC 269 -3A



LIMITS FOR PRE-ARCING TIME			
I_n	1.0 In.	1.6 In.	1.9 In.
	MIN	MIN	MAX
1A - 13 A	1000 hrs	30 min.	30 min.

PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS



FUSES & FUSEHOLDERS

6.3x32mm (1/4"x1/4") Glass and Ceramic Fuses

6.3x32mm Quick Blow Glass Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CF06332F/100	100mA	CF06332F/2.5	2.5A
CF06332F/125	125mA	CF06332F/3	3A
CF06332F/160	160mA	CF06332F/3.15	3.15A
CF06332F/200	200mA	CF06332F/4	4A
CF06332F/250	250mA	CF06332F/5	5A
CF06332F/500	500mA	CF06332F/6.3	6.3A
CF06332F/750	750mA	CF06332F/7	7A
CF06332F/1	1A	CF06332F/7.5	7.5A
CF06332F/1.25	1.25A	CF06332F/8	8A
CF06332F/1.5	1.5A	CF06332F/10	10A
CF06332F/2	2A	CF06332F/15	15A

- Quick blow (F)
- Glass cartridge, nickel plated end caps
- Break capacity, 35A/250V (to 1A), 100A/250V (to 3.5A), 200A/250V (above 3.5A)
- To IEC 127

CF06332F




6.3x32mm Time Delay Glass Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CF06332T/100	100mA	CF06332T/2.5	2.5A
CF06332T/125	125mA	CF06332T/3	3A
CF06332T/160	160mA	CF06332T/3.15	3.15A
CF06332T/200	200mA	CF06332T/4	4A
CF06332T/250	250mA	CF06332T/5	5A
CF06332T/500	500mA	CF06332T/6.3	6.3A
CF06332T/750	750mA	CF06332T/7	7A
CF06332T/1	1A	CF06332T/7.5	7.5A
CF06332T/1.25	1.25A	CF06332T/8	8A
CF06332T/1.5	1.5A	CF06332T/10	10A
CF06332T/2	2A	CF06332T/15	15A

- Time delay (T)
- Glass cartridge, nickel plated end caps
- Break capacity, 35A/250V (to 1A), 100A/250V (to 3.5A), 200A/250V (above 3.5A)
- To IEC 127

CF06332T




6.3x32mm Quick Blow Ceramic Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CF06333CF/100	100mA	CF06333CF/3.15	3.15A
CF06333CF/250	200mA	CF06333CF/4	4A
CF06333CF/500	500mA	CF06333CF/5	5A
CF06333CF/750	750mA	CF06333CF/6.3	6.3A
CF06333CF/1	1A	CF06333CF/7.5	7.5A
CF06333CF/1.25	1.25A	CF06333CF/8	8A
CF06333CF/1.5	1.5A	CF06333CF/10	10A
CF06333CF/2	2A	CF06333CF/15	15A
CF06333CF/2.5	2.5A	CF06333CF/20	20A
		CF06333CF/25	25A

- Quick blow (F)
- Ceramic cartridge, nickel plated end caps
- Break capacity 1000A
- Sand filled
- cULus (500mA-15A)

CF06333CF




6.3x32mm Time Delay Ceramic Fuses

TYPE NO.	RATING	TYPE NO.	RATING
CF06333CT/100	100mA	CF06333CT/2.5	2.5A
CF06333CT/125	125mA	CF06333CT/3.15	3.15A
CF06333CT/160	160mA	CF06333CT/4	4A
CF06333CT/200	200mA	CF06333CT/5	5A
CF06333CT/250	250mA	CF06333CT/6.3	6.3A
CF06333CT/315	315mA	CF06333CT/7	7A
CF06333CT/400	400mA	CF06333CT/7.5	7.5A
CF06333CT/500	500mA	CF06333CT/8	8A
CF06333CT/750	750mA	CF06333CT/10	10A
CF06333CT/1	1A	CF06333CT/12	12A
CF06333CT/1.25	1.25A	CF06333CT/12.5	12.5A
CF06333CT/1.5	1.5A	CF06333CT/15	15A
CF06333CT/2	2A	CF06333CT/20	20A
		CF06333CT/25	25A


- Time delay (T)
- Ceramic cartridge, nickel plated end caps
- Break capacity 1000A
- Sand filled
- cULus (500mA-15A)

CF06333CT




FUSES & FUSEHOLDERS


CF0520F




CF0520T



CF0521CF



CF0521CT



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS



+44 (0)1638 716101
info@camdenboss.com
www.camdenboss.com

We operate a constant improvement policy,
our products are subject to change without notice.


Ver 1.0

CAMDENBOSS
ELECTRONICS & ENCLOSURES


FUSES & FUSEHOLDERS

- PCB TERMINAL BLOCKS
- INTER-CONNECTION
- FUSES & FUSE-HOLDERS
- LEDs & INDICATORS
- MINIATURE SWITCHES
- LIMIT & SAFETY SWITCHES
- CONTROL PRODUCTS
- INTERFACE MODULES & SUPPORTS
- RELAY BASES
- ENCLOSURES
- BATTERIES
- TRANSFORMERS


CF06332F



CF06332T



CF06333CF



CF06333CT

