




ASTAF040VAS0002E04

Connection technology



Product characteristics

Cable plug
M8 connector
Free from silicone
Gold-plated contacts
For hygienic and wet areas in the food industry

Electrical data	
Electrical design	AC/DC
Operating voltage [V]	50 AC / 60 DC
Current rating [A]	3
Protection class	III

Environment	
Ambient temperature [°C]	-25...80, cULus: max. 50 °C
Ambient temperature (moving) [°C]	5...80, cULus: max. 50 °C
Protection	IP 65 / IP 67 / IP 68 / IP 69K

Mechanical data	
Design	angled
Material body	housing: PVC orange
Material nut	stainless steel 316L / 1.4404
Tightening torque for knurled nut [Nm]	0.3...0.5 *)

Drag chain suitability	<p>Bending radius for flexible applications:</p> <p>min. 10 x cable diameter max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s<sup>2</sup></p> <p>Travel speed: 5 m/s<sup>2</sup></p> <p>Bending cycles: &gt; 1 million</p> <p>Torsional strain: ± 180 °/m</p>
Weight [kg]	0.084

Electrical connection	PVC cable / 2 m;
Connection	4 x 0.34 mm <sup>2</sup> (42 x Ø 0.1 mm); Ø 4.9 mm
Sheath colour	orange

**Wiring**

- Core colours
- BK black
  - BN brown
  - BU blue
  - WH white



1	BN
2	WH
3	BU
4	BK

Remarks	*) Take into account the maximum value of the counterpart!
Remarks	

**EVT220 - Cable plug - eclass: 27279201 / 27-27-92-01**

Pack quantity [piece] 1

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — EVT220 — 27.09.2010