



Balloon/storage container 10 L with scale with UV protection, natural-coloured



Description:

Carboys 10 litres, with blue scale, natural-coloured, extra-thick walls, made of fracture-proof polyethylene

- large opening (50 mm diameter) allows easy filling, emptying and cleaning
- captive screw cap
- useful as settling bottle
- resistant to greases, resins, alkalis, oils and acids
- UV protection for long life
- opening sealed with screw plug for screwing in spigots and corner valves (wide thread 22 mm)
- on request: Custom-made product without screw plug opening, print, labelling, individual scales and colours possible
- separate accessories: Spigots (art. no. 550100 + 560100), corner valves (art. no. 520100 + 520700)
- Replacement parts: Carrying handle, screw cap (diameter 65 mm) and plug set consisting of screw caps and 2 seals
- food-safe, resistant to temperature: -20°C to +70°C and free from bisphenol A (BPA)
- w = inside diameter of filling opening = 50 mm / a = outside thread diameter = 65 mm
- Diameter d=210 mm / height h=427 mm

Information:

Article

Articlenumber	823410
GTIN	4007228823417
Customs tariff	39233090
Packaging Unit (PU)	4

Colour	natural
Volume in l	10
Weight (kg)	0,88
T x B x H (mm)	210 x 210 x 427

Outer packaging

Content in pieces	4
L x B x H (mm)	530 x 395 x 545

Gross weight unit (kg)	4,12
------------------------	-------------

Pallet

Number of boxes	16
Number of layers	4
L x B x H (m)	1,2 x 0,8 x 2,33

Carton per layer	4
Gross Weight Palette (kg)	85,92