



Datenblatt - Fiche technique - Data sheet


11.04.5665



ROLINE Monitor-Kabel mit Ferritkern+DDC, HD15 ST-ST, 15m

ROLINE Câble écran HD15 M/M avec noyaux de ferrite + DDC, 15 m

ROLINE High Quality VGA Cable + Ferrite + DDC, HD15, M/M, 15 m




NOTES:

- 1) P1 & P2 HD 15 Male / Male
- 2) FULLY COPPER FOIL SHIELD 360° P1 & P2.
- 3) CABLE JACKET : PVC BLACK COLOR
- 4) MOLDED HOOD : BLACK COLOR
- 5) PIN 9 & PIN 15 CONNECTED
- 6) RoHS & REACH COMPLIANT
- 7) 2 x FERRITE CORE, BLACK COLOR

SHORT AND OPEN 100% TESTING
 CONDUCTOR RESISTENCE 5Ω
 INSULATION RESISTENCE 20MΩ
 HI-POT: DC 250V

PINOUT:



4	INNER JACKET: PE (RoHS)
3	OUTER JACKET PVC 45Pa BLACK(1101)(RoHS)
2	HDB15M BLUE SOLDER TYPE TERMINAL BRASS GOLD FLASH (RoHS)
1	2919 28#3CO+28#9C+ADB(AL/MG) OD:8.0 BLACK(1101) 15000MM (RoHS)

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE: #/0°		rotronic				
DIMENSIONS	TOLERANCE					
0.00 TO 30.00mm	±0.10mm	ROLINE HQ VGA Cable, w/Ferrite & DDC, HD 15 M/M 15m, black				
30.01 TO 80.00mm	±0.15mm					
80.01 TO 150.00mm	±0.15mm					
150.01mm	±0.20mm	11.04.5665				
MATERIAL		SCALE	SHEET 1/1	UNIT MM	SIZE A4	REV. A
FINISH						