

Product information

03 06 180 T

Combination Pliers

DIN ISO 5746 IEC 60900 DIN EN 60900

- Pliers with integrated, insulated tether attachment point for a tool tether
- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General

Article No.	03 06 180 T
EAN	4003773081395
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	270 g
Dimensions	180 x 57 x 27 mm
Standard	DIN ISO 5746 DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 3.4 mm
Cutting capacities hard wire (diameter)	Ø 2.2 mm
Cutting capacity copper cable, multiple-stranded	Ø 12.0 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm ²
Drop Protection System	yes
VDE tested	yes

technical change and errors excepted



