

Product information

71 41 200

KNIPEX CoBolt®

Compact Bolt Cutter



- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to Ø 5.2 mm
- Efficient joint design ensures exceptional cutting performance with little effort
- With recess for easier cutting of thicker wires
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- 20° angled head with joint bar on one side and side cutter for almost flush cutting, with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

Article No.	71 41 200
EAN	4003773066897
Pliers	black atramentized
Handles	plastic coated
Weight	335 g
Dimensions	200 x 62 x 24 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities soft wire (diameter)	Ø 6 mm
Cutting capacities medium hard wire (diameter)	Ø 5.2 mm
Cutting capacities hard wire (diameter)	Ø 4.0 mm
Cutting capacities piano wire (diameter)	Ø 3.6 mm

technical change and errors excepted

