



Straight power contacts for cable applications

| Identification | Rating (A) | Part No. | |
|-----------------------------------|----------------------|--|--|
| Performance levels ▶ | | Performance level 3 | S4¹⁾ |
| Solder version | | | |
| Male contacts | 10 20 30 40 | 09 69 281 7420 09 69 281 7421 09 69 281 7422 09 69 281 7423 | 09 69 281 5420 09 69 281 5421 09 69 281 5422 09 69 281 5423 |
| Short male contacts | 20 40 | 09 69 281 7821 09 69 281 7823 | 09 69 281 5821 09 69 281 5823 |
| Female contacts | 10 20 30 40 | 09 69 181 7420 09 69 181 7421 09 69 181 7422 09 69 181 7423 | 09 69 181 5420 09 69 181 5421 09 69 181 5422 09 69 181 5423 |
| Short female contacts | 20 40 | 09 69 181 7821 09 69 181 7823 | 09 69 181 5821 09 69 181 5823 |
| Crimp version²⁾ | | | |
| Male contacts | 10 20 30 40 | 09 69 282 7420 09 69 282 7421 09 69 282 7422 09 69 282 7423 | 09 69 282 5420 09 69 282 5421 09 69 282 5422 09 69 282 5423 |
| Short male contacts | 20 40 | 09 69 282 7821 09 69 282 7823 | 09 69 282 5821 09 69 282 5823 |
| Female contacts | 10 20 30 40 | 09 69 182 7420 09 69 182 7421 09 69 182 7422 09 69 182 7423 | 09 69 182 5420 09 69 182 5421 09 69 182 5422 09 69 182 5423 |
| Short female contacts | 20 40 | 09 69 182 7821 09 69 182 7823 | 09 69 182 5821 09 69 182 5823 |

D-Sub

¹⁾ S4 = 0.76 µm Au or PdNi equivalent
²⁾ Tooling see chapter 20