


CUSTOMER	CPC
PRODUCT NO.	CS287**Series
HENTEK NO.	HK-USB3.1AFC01-*Series



PRODUCT NO.	CS28737	CS28738
HENTEK NO.	HK-USB3.1AFC01-1	HK-USB3.1AFC01-2
$L \pm T$ (mm)	$1000 \pm 10$	$2000 \pm 20$


SIDE:A

SIDE:B

NOTE:

- (1). Cable Spec: (30AWG\*1P+DAM)\*2+30AWG\*1P+28AWG\*2C  
Jacket Material:PVC OD:4.6±0.2mm  
Colour: Black
- (2). Connector A: USB3.1 C MALE Solder type  
Insulation:Black  
Contacts:Gold Plated  
Shell:Nickel Plated
- (3). Connector B: USB3.1 A FEMALE Solder type  
Insulation:Blue  
Contacts:Gold Plated  
Shell:Nickel Plated
- (4). Over Mold Colour: PVC-Black
- (5). Parameter Settings: CT-8681FA  
1. Insulation Resistance:5MΩ (MIN.)  
2. Conductive Resistance:2.0Ω (MAX.)
- (6). 100% OPEN, SHORT&MISWIRE TEST
- (7). PACKING:PEBAG PACKING.

<u>SIDE:A</u>		<u>SIDE:B</u>
USB CM		USB AF
A4+B4+A9+B9	red	1
A6	white	3
A7	green	2
A1+B1+A12+B12	black	4+7
A2	blue	9
A3	yellow	8
A1+B1+A12+B12	drain	4+7
B10	orange	5
B11	purple	6
A1+B1+A12+B12	drain	4+7
Shell	braid	Shell



PIN OUT: (5)

PACKING: (7)

GENERAL TOLERANCES (UNLESS SPECIFIED)							
LENGTH: X ± 1 .X ± 0.2 .XX ± 0.10 ANGLE: X° ± 1° .X° ± 0° 30'	UNIT: mm	REV: 0/A			NAME	USB3.1 C MALE/A FEMALE	
	DRAWING	XIAODENG	2015/5/21	S. P. NO.	HT-6488	DWG. NO.	
	CHECK			P. O. NO.		PAGE	1/1
	APPROVE			SIZE			

00	NEW	2015/5/21
REV	DESCRIPTION	DATE