

# Han 3A-AK



Part number	09 20 003 5428
Specification	Han 3A-AK
HARTING eCatalogue	https://b2b.harting.com/09200035428

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Series of hoods/housings	Han A <sup>®</sup>
Type of accessory	Protection cover
Description of the accessory	for cable to cable housing Metal With fixing cord

### Version

Size	3 A
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



## Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL	
-----------	--------	--

#### Commercial data

Commercial data	
Packaging size	10
Net weight	22.6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140038967
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors