

Inset Trend 75 Swing IP23

INSET TREND 75 SW ES50 WH EX-LMP
3083500



Product features

- 75mm cut out. 2 x 30° Tilt. Round bezel.



PRODUCT OVERVIEW

Product name	INSET TREND 75 SW ES50 WH EX-LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number SE	7463875
Warranty	3 years
LOR (%)	Dependent on lamp
Light colour	N/A
Light source included	Fixture without Lightsource
Electrical protection	Class II
Housing colour	White
IP rating	IP23/20
IK rating	IK02
Product EAN number	8711971835004

DATA TABLE

General data

Product name	INSET TREND 75 SW ES50 WH EX-LMP
Technology	LED/Halogen
Cap/Base	GU10
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Residential & Consumer
ETIM Class	EC001744
E-number SE	7463875
Warranty	3 years

Inset Trend 75 Swing IP23

INSET TREND 75 SW ES50 WH EX-LMP
3083500

Optical data

LOR (%)	Dependent on lamp
Light colour	N/A
Adjustable chromaticity	N

Electrical data

Light source included	Fixture without Lightsource
Mains voltage (V)	220-240V
Electrical protection	Class II
Transformer required	No
Nominal Frequency (Hz)	50/60Hz

Physical data

Housing colour	White
IP rating	IP23/20
IK rating	IK02
Nominal Product Length (mm)	83
Nominal Product Width (mm)	83
Nominal Product Height (mm)	85
Cutout Dimensions (W x L in mm or Diameter in mm)	75
Weight (kg)	0.25
Recessed Depth (mm)	100

Packaging

Single packaging type	Carton
Product EAN number	8711971835004
Packaging single length / height (cm)	14.0
Packaging single width (cm)	11.0
Packaging single depth (cm)	7.0
DUN14 (outer)	18711971835001
Units per outer package	1
Packaging outer length / height (cm)	14.0
Packaging outer width (cm)	11.0
Packaging outer depth (cm)	7.0

TECHNICAL DRAWINGS

