

Adjustable clamps

Depressed centre



Version:

- Heat-treated steel
- Painted
- Single depressed centre



Art. no.	26138 050
Slot width	18 mm
Length	125 mm
Suitable cheese-head screw DIN 912	M16, M18
Slot length	40 mm
Clamping shoe height	25 mm
Clamping shoe width	50 mm
Height	23 mm
Width 3	25 mm
Height 2	20 mm
DIN	6316

EAN-Code

4020772071066