

Spirit level with second vertical bubble

Model: BMI Robust

BMI

Application:

For horizontal and vertical alignment of an object



Execution:

- Model: BMI Robust
- With ultrasonically welded bubble vials and non-glare reading
- Reverse measuring possible (0.5 mm/m)
- 2 milled measuring surfaces up to 200 cm
- Particularly large, shock-absorbing rubber end caps

Advantage:

- Edgeless horizontal spirit level for undistorted view of bubble, even during reverse measuring
- Life-long high measuring accuracy (0.5 mm/m) through ultrasonically welded levels
- Extremely torsion-resistant thanks to multi-chamber profile (profile cross-section 30 x 65 mm)

Art. no.	38638 100
Brand	BMI
Manufacturer Part Number	638100PS
Length	1000 mm
Measuring accuracy (per length)	0.5 mm/m
Gross Weight	1.060 kg
Product Group	384

EAN

4007368119586