

## Drawer cabinet S – with fully extending drawers

Height 1036 mm, width 722 mm, depth 700 mm

**ORION**<sup>®</sup>

### Application:

Ideally suited to the storage of various tools and parts.

### Execution:

- Welded sheet-steel construction guarantees high loadability and stability
- Central locking mechanism with safety lock and individual extension lock for drawers
- Drawers capable of holding an evenly distributed load of up to 100 kg
- Drawers with rows of slots for inserting dividers
- Grid division (30:30 mm) facilitates custom compartmentalisation of drawers in housing
- Plastic-coated worktop (black) with a thickness of 8 mm
- Handle strips made from aluminium with labelling strips with transparent covers and cover caps



<b>Art. no.</b>	<b>50100 071</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	50100071
<b>Number of drawers</b>	7 PCS
<b>Height</b>	1036 mm
<b>Width</b>	722 mm
<b>Depth</b>	700 mm
<b>Height x width x depth</b>	1036 x 722 x 700 mm
<b>Drawer width (inner dimension) x drawer depth (inner dimension)</b>	599 x 598 mm
<b>Drawer with slots</b>	Yes
<b>Perforated drawer base</b>	No
<b>Load-carrying capacity per drawer</b>	100 kg
<b>Drawer surface</b>	0.385 m <sup>2</sup>
<b>Pullout type</b>	Full extension
<b>With SOFT-CLOSE closing function</b>	No
<b>With single pull-out safety brake</b>	Yes
<b>Central locking</b>	Yes
<b>With cover panel</b>	Yes
<b>Material of cover panel</b>	Wood, plastic-coated
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Light grey RAL 7035
<b>Surface</b>	Powder-coated
<b>Functions</b>	RFID possible
<b>Overall surface</b>	2.695 m <sup>2</sup>
<b>Lock type</b>	Cylinder lock
<b>Material</b>	Sheet steel
<b>Gross Weight</b>	97.000 kg
<b>Product Group</b>	586

### EAN

4053625364961