

Pneumatic drill machine RR-13DP



Version:

- Ergonomic shape
- Left and right rotation
- Noise-dampened air outlet through the handle

Delivery:

Includes quick-action drill chuck and side handle



Art. no.	75066 103
Model	RR-13DP
Max. drilling diameter in steel	13 mm
Max. idle speed	800 rpm
Power rating	350 W
Air consumption	8 l/s
Connection thread	1/4 inch
Min./max. drill chuck span width	1.5-13 mm
Inner hose diameter	10 mm
Weight	1.3 kg
With right/left-hand rotation	Yes
Operating pressure	6.3 bar
Length	218 mm
Sound-pressure level	83 dB

EAN-Code

8717981197477