



EcoClassic30 Reflector

EcoClassic30 28W E14 230V NR50 FR 1CT

Energy-saving mains-voltage halogen lamp in classic NR50/NR63 reflector shapes

Product data

• General Characteristics

| | |
|------------------------|----------------------------|
| Cap-Base | E14 |
| Bulb | NR50 [NR 50mm] |
| Bulb Finish | Frosted |
| Operating Position | any [Any or Universal (U)] |
| Rated Lifetime (hours) | 2000 hr |

• Electrical Characteristics

| | |
|--------------------------------|--------------------|
| Lamp Wattage | 28 W |
| Lamp Wattage Technical | 28 W |
| Voltage | 230 V |
| Lamp Current | 0.12 A |
| Dimmable | Yes |
| Wattage Equivalent | 40 W |
| Rated Wattage | 28 W |
| Starting Time | 0.01 (max) s |
| Warm-up Time to 60% Light Outp | instant full light |

• Environmental Characteristics

| | |
|----------------------|--------|
| Mercury (Hg) Content | 0.0 mg |
|----------------------|--------|

• Light Technical Characteristics

| | |
|-----------------------|--------------|
| Beam Angle | 30 D |
| Beam Angle Technical | 30 (min) D |
| Luminous Intensity | 400 (max) cd |
| Color Rendering Index | 100 Ra8 |

| | |
|-----------------------------|--------|
| Color Temperature | 2800 K |
| Color Temperature Technical | 2800 K |

• Product Dimensions

| | |
|------------------|---------------|
| Overall Length C | 86.5 (max) mm |
| Diameter D | 51 (max) mm |
| Overall Width E | 51 (min) mm |
| Overall Height H | 86.3 (min) mm |

• Measuring Conditions

| | |
|-----------------|-------|
| Switching cycle | 8000X |
|-----------------|-------|


• Product Data

| | |
|-----------------------------|--|
| Order code | 925640044201 |
| Full product code | 925640044201 |
| Full product name | EcoClassic30 28W E14 230V NR50 FR 1CT |
| Order product name | EcoClassic30 28W E14 230V NR50 FR 1CT/10 |
| Pieces per pack | 1 |
| Packing configuration | 10 |
| Packs per outerbox | 10 |
| Bar code on pack - EAN1 | 8727900252743 |
| Bar code on outerbox - EAN3 | 8727900661989 |
| Logistic code(s) - 12NC | 925640044201 |
| Net weight per piece | 20.800 gr |


PHILIPS

sense and simplicity

Dimensional drawing



| Product | C (Max) | D (Max) |
|----------------------------------|---------|---------|
| EcoCl30 28W E14 230V NR50 30D FR | 86.5 | 51 |



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, July 20
data subject to change