



**PCT-0150-030-OR-100**

Cable Tie, 150x3.2mm, Orange Plastic Barb

Cable ties in high industrial quality with rounded edges to prevent cable damage. Inclined tip to indicate usage direction and quick installation time. Material: Polyamid 6.6 Temp range: -40 degrees Celsius to +85 degrees Celsius Flammability rating: UL94-V2



## Product Properties:

<b>Model</b>	Internal toothing
<b>Material quality</b>	Polyamide (PA)
<b>Band closure</b>	Plastic lip/-cam
<b>UV-stable acc. ASTM D6779</b>	No
<b>Transparent</b>	No
<b>Solvable fastener</b>	No
<b>Text strip</b>	None
<b>Type of fastening</b>	None
<b>Colour</b>	Orange
<b>Surface protection</b>	Untreated
<b>Material</b>	Plastic
<b>Halogen free</b>	Yes
<b>Inflammability class of insulation material according to with UL94</b>	V2
<b>Operating temperature</b>	-40-85 °C
<b>Max. tensile force</b>	180 N

## Dimensions:

<b>Unit</b>	pcs
-------------	-----

Length belt/tape/tie	150 mm
Band width	3.3 mm
Max. bundle diameter	38 mm
Max. tensile force	180 N
MOQ	100 .

### **Approvals:**

Approved according to CE	Yes
Approved according to UR	Yes
With approval according to UL	Yes
Inflammability class of insulation material according to with UL94	V2

### **Compliance:**

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (233 Subs. Jan 2023)
SCIP	Not Applicable

### **Other information:**

Trademark	NEMIQ
ETIM-Class	EC000046 - Cable tie
ETIM-Release	7.0
Product Group	Standard Cable ties
Alternative SKU	PCT-0150-030-OR-100

### **Logistic information:**

Barcode	733117640058
Country of origin	TW
Item status	Stock item, normally in stock with reservation for in between sales., Non Stock Item, can be on stock but is not a regular stock item.
Stock code	PCT-0150-030-OR-100
Taric code	39269097
Unit	pcs
MOQ	100 .