

# ROLINE S/FTP Cable Cat.7, with RJ-45 connectors (500 MHz / Class EA), LSOH, grey, 0.5 m

<b>Product No.</b>	21.15.0854
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	21.15.0854
<b>EAN (single piece)</b>	7611990110643

**roline**  
Designed for Professionals



**Cat.6A**  
Class EA

**S/FTP**

**LSOH**

**The right solution for a network connection with data transfer rate up to 10 Gbit/s, at a frequency of 500 MHz**

- Patch cord for networking connections between devices
- Prepared shielded Twisted Pair cable (PiMF) with Shielded RJ-45 connectors on both ends
- Durable due to moulded kink protection
- Flexible cable, suitable for narrow bending
- Impedance: 100 Ohm
- Colour: grey
- Contact settings 1:1, in accordance with the EIA/TIA 568 standard
- Construction: 8 lines + pairs shielded with aluminium foil, complete shielding in tinned copper braid

## Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	S/FTP Patchcord
Colour	grey

Length	0.5 m
Shield type	SFTP
Transfer quality	Cat6A / Class EA
Impedance	100 Ohm
Quantity of wires	8
Conductor type	Wire
Crossed	No
Colour (Spout)	grey
Cable LSOH	Yes
Side 1 Connector Type	RJ-45
Side 1 Connector Gender	Male
Side 2 Connector Type	RJ-45
Side 2 Connector Gender	Male
Connector Type RJ45	Standard
Weight	27.1 g