


KSSG3108



Additional Info

FO (Hz):	1,250+/-200@1.0V
Rated Input (W):	0.1
Sound Pressure Level (dB):	95+/-3dB(0.1W/10cm), 85+/-3dB(1W/1m)@1.5K, 2.0K, 2.5K, 3.0KHz
Maximum Input (W):	0.2
Impedance (Ω):	8+/-20%@1.5KHz 1.0V
Frequency Range (Hz):	Fo---4K
Operating Temp (C):	-20~+55
Dimension (mm):	Φ 31.8x20.5