


H0,75/14D GR BD



Similar to illustration

General ordering data

Type	H0,75/14D GR BD
Order No.	9004300000
Version	Wire end ferrule, insulated, 10 mm, 8 mm, Grey
GTIN (EAN)	4008190154837
Qty.	500 pc(s).
Packaging	Reel packaged

Dimensions and weights

Width	14 mm
Width (inches)	0.551 inch
Net weight	0.086 g

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	2.8 mm
Colour code	DIN
Conductor cross-section	0.75 mm ²
Contact surface diameter (D1)	1.2 mm
Contact surface length (L2)	8 mm
L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm

Military designation	T 20A 005 A
Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 18

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S

Classifications

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005
ETIM 6.0	EC000005
UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01

Approvals

Approvals	
ROHS	Conform
UL File Number Search	E354986

Related products:



Type: H0,75/14 W BD
 Order No.: 9004290000
 Description of article: Strip of wire end ferrules, white


Version:
 Wire end ferrule, insulated, 10 mm, 8 mm, White

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/14T HBL BD
 Order No.: 9004310000

Version:
 Wire end ferrule, insulated, 10 mm, 8 mm, Light Blue

Description of article: Wire-end ferrule



[PDF data sheet](#) [Add to Inquiry List](#)