

Gro-Lux T5 FHO24W/GRO 0002740



Product features

- High level of blue and red radiation helps promote healthy plant growth. Enhanced the natural colours of aquatic plants and fish in aquariums. For lighting of fresh water aquarium.



PRODUCT OVERVIEW

Product name	FHO24W/GRO
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T5
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Hospitality, Retail, Residential & Consumer
ETIM Class	EC000108
E-number Norway	3801037
Luminous flux (lm)	650
Light colour	Grolux
Wattage (W)	24.00
Product Voltage (V)	75
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	15000
Product EAN number	5410288027401

DATA TABLE

General data

Product name	FHO24W/GRO
Technology	Fluorescent
Lamp shape	Tubular shape
Type	T5
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Hospitality, Retail, Residential & Consumer
Operating temperature range (°C)	-15°C...+50°C
ETIM Class	EC000108

Gro-Lux T5 FH024W/GRO 0002740

E-number Norway	3801037
-----------------	---------

Optical data

Luminous flux (lm)	650
Ambient temperature for maximum luminous flux (°C)	35
Light colour	Grolux
Adjustable chromaticity	N

Electrical data

Wattage (W)	24.00
Watt (Rated) - High frequency (W)	23.50
Current (A)	0.300
Product Voltage (V)	75
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	300

Lifetime data

Average life (Nominal) (h)	15000
----------------------------	-------

Physical data

Nominal Product Length (mm)	550.0
Nominal Product Diameter (mm)	16
Max. Length base to base (mm) - A	549.0
Length base to pin Min-Max (mm) - B	553.7-556.1
Max. Lamp Length (mm) - C/L	563.2
Max. Lamp Diameter (mm) - D	17.0
Weight (kg)	0.043

Packaging

Single packaging type	Carton
Product EAN number	5410288027401
Packaging single length / height (cm)	56.4
Packaging single width (cm)	1.9
Packaging single depth (cm)	1.9
DUN14 (outer)	15410288027408
Units per outer package	25
Packaging outer length / height (cm)	57.8
Packaging outer width (cm)	10.5
Packaging outer depth (cm)	10.5

Safety data

Lamp mercury content (mg)	2.30
Optimal operating condition (°C)	-15-50
Breakage cleaning instructions	Applicable
Special purpose lamp	Yes

Gro-Lux T5
FH024W/GRO
0002740

Suitable for household illumination
Safety message

No
Not suitable for household

TECHNICAL DRAWINGS

