

Monitor LED

MONITOR IP55 IK10 1377LM 830 BLACK EM3

4063826



Product features

- Led exterior bulkhead, Unique feature allowing a choice between High Output or High Efficiency with the flick of a switch, die-cast aluminium body, 717/1377LM, 9/17W, 80/81LM/W, 4000K, Driver Current: 350/750mA, CRI80, Non dimmable, Emergency, IP55,IK10, lifespan 100,000hrs (L70:B50), (HxWxD)350 x 350 x 128mm, 4kg, 3 step MacAdam ellipse, RAL 9005, Class 1, 230V, energy class: A++, A+, A



PRODUCT OVERVIEW

Product name	MONITOR IP55 IK10 1377LM 830 BLACK EM3
Technology	LED
Environment	Indoor, Outdoor
General application	Education, Hospitality, Logistics & Industry, Office, Residential & Consumer, Retail
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	717/1377
Luminaire efficacy (lm/W)	72
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Photobiological Risk Group	RG1
Total power consumption (W)	11/19
Electrical protection	Class I
Dimmable	No
Housing colour	Black
IP rating	IP55
IK rating	IK10
Product EAN number	5026524638265

DATA TABLE

General data

Product name	MONITOR IP55 IK10 1377LM 830 BLACK EM3
Technology	LED
Environment	Indoor, Outdoor
General application	Education, Hospitality, Logistics & Industry, Office, Residential & Consumer, Retail
ETIM Class	EC002892
Warranty	5 years

Monitor LED

MONITOR IP55 IK10 1377LM 830 BLACK EM3
4063826

Optical data

Fixture luminous flux (lm)	717/1377
Luminaire efficacy (lm/W)	72
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Photobiological Risk Group	RG1
Emergency duration (h)	3

Electrical data

Total power consumption (W)	11/19
Mains voltage (V)	230-240V
Lamp power factor	0.95
Electrical protection	Class I
Dimmable	No
Drive current (mA)	700
Inrush Current (A)	17
Inrush Duration (µs)	199
Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	38
Max. Luminaires per 13A C Breaker	50
Max. Luminaires per 16A C Breaker	61
Max. Luminaires per 20A C Breaker	78
Max. Luminaires per 10A B Breaker	23
Max. Luminaires per 13A B Breaker	30
Max. Luminaires per 16A B Breaker	37
Max. Luminaires per 20A B Breaker	47

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

Physical data

Housing colour	Black
IP rating	IP55
IK rating	IK10
Diffuser finish	Opal
Diffuser material	PC Polycarbonate
Nominal Product Width (mm)	129
Nominal Product Height (mm)	350
Weight (kg)	4.2

Packaging

Single packaging type	Carton
Product EAN number	5026524638265

Monitor LED

MONITOR IP55 IK10 1377LM 830 BLACK EM3
4063826


Packaging single length / height (cm)	36.0
Packaging single width (cm)	36.0
Packaging single depth (cm)	13.5
DUN14 (outer)	05026524638265
Units per outer package	1
Packaging outer length / height (cm)	36.0
Packaging outer width (cm)	36.0
Packaging outer depth (cm)	13.5

PHOTOMETRY

Distance [m]	Cone diameter [m]	E(0°)	E(C90)	E(C0)	Illuminance [lx]
0.5	1.53 1.53	219	18	18	
1.0	3.06 3.07	55	5	4	
1.5	4.59 4.60	24	2	2	
2.0	6.11 6.14	14	1	1	
2.5	7.64 7.67	9	1	1	
3.0	9.17 9.20	6	1	0	

Distance [m] Cone diameter [m] Illuminance [lx]

— C0 - C180 (Half beam angle: 113.6°)
— C90 - C270 (Half beam angle: 113.6°)



TECHNICAL DRAWINGS

